

## Nadi Oksimeter Jari / Fingertip Pulse Oximeter

Model: SB200



Product Reg. No.: GC6493119-36113



Pelindung Cahaya Ambien /  
Blocks Ambient Light



Pemantauan Berterusan /  
Continuous Monitoring



Pemantauan Masa Sebenar /  
Real Time Monitoring

### Teknologi Pemeriksaan Arteri (ACT) / ACT (Artery Check Technology)

Teknologi Pemeriksaan Arteri (ACT) menganalisa nadi dan isyarat SpO2 dan menentukan kekerasan arteri (Kondisi Arteri). ACT mengklasifikasikan kondisi arteri dengan lebih komprehensif kepada 6 tahap.

Artery Check Technology analysis the pulse and SpO2 signals and determines the actually prevailing stiffness of the artery (Artery Condition). ACT further comprehensively classifies the arterial condition into 6 levels.



Level 1



Level 2



Level 3



Level 4



Level 5



Level 6

- Dilengkapi Teknologi Pemeriksaan Arteri /  
Artery Check Technology (ACT) embedded
- Bacaan SpO2 dan Denyutan Nadi Masa Sebenar,  
Kondisi Arteri dalam 1 minit. /  
Real time SpO2 & Pulse Rate Reading,  
Artery Condition in 1 minute
- Reka bentuk perisai pelindung cahaya ambien /  
Shielded Design blocks ambient light
- Perlindungan Biokompatibiliti & Reka Bentuk  
anti-alergi / Biocompatibility & Anti-Allergic Design
- Indikasi Kekuatan Nadi /  
Pulse Strength Indicator
- Penggera boleh dilihat & didengar /  
Visible & audible alarm
- Paparan OLED dua arah & dua warna /  
Two way, two color OLED display
- Tali penyambung /  
Cord-attached
- Sesuai untuk penilaian terapi oksigen /  
Ideal for oxygen therapy assessment
- Sesuai untuk pengurusan kesihatan /  
Ideal for health management
- Sesuai untuk pemeriksaan setempat &  
pemantauan berterusan /  
Ideal for spot-check & continuous monitoring



Teknologi  
Pemeriksaan Arteri /  
Artery Check  
Technology



Bacaan SpO2 &  
Denyutan Nadi /  
SpO2 & Pulse  
Rate Reading



Perlindungan  
Biokompatibiliti &  
Reka Bentuk anti-alergi /  
Biocompatibility &  
Anti-Allergic Design



Indikasi  
Kekuatan Nadi /  
Pulse Strength  
Indication



Penggera boleh  
didengar & dilihat /  
Visible & Audible  
Alarm



Paparan OLED dua  
arah & dua warna /  
OLED Two-way  
Two-Color Display



Tali Penyambung /  
Cord Attached

### Spesifikasi / Specification

Julat Pengukuran / Measurement Range | SpO2: 35%~99%; PR: 30~250 bpm  
Ketepatan / Precision | SpO2: 70%~99%; ±2%; 35%~69% (tidak ditentukan /  
unspecified); Denyutan nadi / Pulse rate: 30~250bpm; ±3  
Penggera / Alarm | Nilai Asai bagi SpO2 / Default Value for SpO2  
Sumber Kuasa / Power Supply | 2" AAA" Alkaline

Rossmax InnoTek Corp.  
CEC REP CMC Medical Devices & Drugs S.L.  
C/ Horacio Lengo Nº 18, CP 29006,  
Málaga, Spain

CSMB\_Epaper\_SB200\_ver2021